


L2 Module Connector (via flat flex cable to ConnectorBoard)




CON10
Molex 502598-3393



NOTE:
CON10 has reversed signal assignments to pin numbers to connect via 1:1 flat flex cable to ConnectorBoard!

Flat Flex Cable:
33 pos, Molex 150150233 (50.8 mm)

L2 Module Connector (from L2 Modules)



CON20
Molex 502598-3393



- FID10 Fiducial
- FID11 Fiducial
- FID12 Fiducial

Adapter Board L2 Module to L2 Module	
System: CMS LEA TESTING	
Board: ADAPTER_L2_L2	
Created: 12-JAN-2016, Daniel Florin	Revision: 1.0
Modified: 12-JAN-2016, Daniel Florin	Sheet: 1 of 1
Physik Institut Universitaet Zurich Winterthurerstrasse 190 8057 Zurich	